



BLT Circuit Services Ltd  
Brome Ind. Est. Brome, Eye,  
Suffolk, IP23 7HN, England  
Tel: 01379 870870  
Fax: 01379 870970  
e-mail:sales@blt.keme.co.uk  
www.bltcircuitservices.co.uk

## BLT Flux Pens

### Refillable Flux Pens

#### Description

**BLT Refillable Pens** are available with 3 different applicator heads. Fine, medium and coarse to suit customer requirements. The pens are ideal for SMT, rework and repair on assembled circuit boards. The pens are compatible with Alcohol based and VOC Free Fluxes. They are colour coded for easy identification; Fine-yellow, Medium-green and Coarse-purple.

Stock Codes	Fine	2359FI
	Medium	2359ME
	Coarse	2359LA



### Instructions for use

- 1) Unscrew the applicator head from the barrel.
- 2) Gently squeeze the “push” panels on the sides of the barrel and immerse in flux.
- 3) Release the “push” panels and the flux will be drawn into the barrel.
- 4) Re-attach the applicator head to the barrel.
- 5) To control the flow of flux adjust the pressure on the barrel.

### BLT No Clean Flux Pens

BLT no clean flux pens contain approximately 20ml of BLT **35-90TX** no clean flux for SMT and rework application. The pens have a tight fitting lid to maximise effective life and have a 4mm x 3mm tip. To activate the flow of flux depress the tip. The pens are not refillable and should be disposed of safely.

Stock Code           23590P

