

HG1360B

Stretch Hook & Loop Heel Grounder

Description

Heel grounding devices provide protection for staff on the move. The HG1360B is constructed from durable materials and features a blue stretch loop closure to maximize fit and comfort.

Heel grounders connect the person wearing them to ground via a proper floor mat or flooring material. Wearing the conductive ribbon inside the shoe or sock assures proper electrical contact with the user. The ribbon connects to the conductive rubber to complete the circuit between the operator and the static controlled floor or mat.

A buried 1 meg ohm resistor is standard. Heel grounders are worn on both feet to provide consistent grounding while in motion.

Meets or exceeds requirements of ANSI ESD-S20.20.



Key Features: • **Stretch Loop closure** • **Buried resistor** • **1.25" cup design**

Product Specifications

Resistor: 1 meg ohm (+/- 5% tolerance), buried
Color: Blue stretch loop, Black/White rubber
Rubber Exterior: <10e5 ohms, 1.25" wide
Ribbon: Conductive yarn in gray polyester ribbon

Product Number

<u>Item Number</u>	<u>Description</u>	<u>Price</u>
HG1360B	Heel Grounder, Blue Stretch loop, 1 meg	\$3.95

Note: Heel grounders are dependent on foot perspiration in the shoe to create and maintain electrical contact with the body. The HG1360B works reliably with stockings and socks due to the moisture present.

This document is prepared for our customers as a service, and is to the best of our knowledge true and accurate. However, it is understood and agreed by the users of this document that we will accept no liability for the conclusions reached. Users of this document may therefore wish to perform additional testing before determining that products mentioned are suitable.



"Delivering More Than Packaging"

CentralPackage.com 763.425.7444