

SPECIFICATION CONTROL DRAWING



ITEM #1: SEALING SLEEVE



ITEM #2: CRIMP SPLICE

MATERIALS

- 1. INSULATION SLEEVE: Heat-shrinkable, transparent blue, radiation cross-linked modified polyvinylidene flouride.
- 2. SINGLE-WIRE SEAL: Immersion resistant thermoplastic.
- 3. THREE-WIRE SEAL: Immersion resistant thermoplastic.
- 4. CRIMP SPLICE: Base metal: Copper Alloy 101 or 102 per ASTM B-75.

Plating: Tin per MIL-T-10727, Type 1.

Color code: See table below.

Dimensions of Crimp Splice:

simulations of examp spinor.										
Part	Prod.		Crimp Splice							
Name	Rev.	Size	ØA	ØB	D	Е	Color Code			
D-436-52	С	16	2.69 (0.106)	1.75 (0.069)	14.86 (0.585)	<u>7.11 (0.280)</u>	Blue			
			2.56 (0.101)	1.63 (0.064)	14.35 (0.565)	6.60 (0.260)				
D-436-53	С	12	3.91 (0.154)	2.59 (0.102)	14.86 (0.585)	<u>7.11 (0.280)</u>	Yellow			
			3.73 (0.147)	2.46 (0.097)	14.35 (0.565)	6.60 (0.260)				

Installation Data:

	Wire Size Range of Crimp Splice								
Splicer	One	Wire	Two	wires	Three wires				
Size	Minimum	Maximum	Minimum	Maximum	Minimum	Maximum			
16	20	16	24	20	24	22			
12	16	12	22	16	22	18			

305				Products	IN-LINE SPLICE SEALING SYSTEM, 2 OR 3 TO 1 SPLICE: Tin Plated, Color Coded, with Inspection Slots					
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.						DOCUMENT NO.: D-436-52/-53				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	ANGLES: N/A ROUGHNESS IN MICRON		drawing at any time. Users should evaluate the suitability of the product for their application.		DATE: 15-Apr-	11	DO	oc issue: 2		
DRAWN BY: M. FORONDA		REPL	ACES: N/A	DCR NUMB	BER: 01302	PROD. REV. SEE TABLE	SCALE: None	SIZE:	SHEET: 1 of 2	

SPECIFICATION CONTROL DRAWING

APPLICATION

- 1. These parts are designed to provide an immersion resistant in-line splices of 2 or 3 to 1 wires falling within the size range listed on sheet 1, having insulations rated for at least 135°C.
- 2. Parts are available only as an assembly of one of each Item #1 and Item #2.
- 3. Parts are to be installed per Thermofit Assembly Procedure, see below.
- 4. Inside diameter and outside diameter of splice are to be measured in crimp areas, 2.54 to 5.08 (0.100 to 0.200) from ends of part. Slight burr permitted on parted surfaces.
- 5. Acceptance sampling shall be in accordance with Paragraph 4.6.1 of MIL-T-7928.
- 6. Packing and packaging shall be in accordance with Section 5, Level C, of MIL-T-7928.
- 7. This document takes precedence over documents referenced herein.

THERMOFIT ASSEMBLY PROCEDURE

1.0 SCOPE

This document outlines the procedure to be followed to obtain immersion resistant 3 or 2 to 1 in-line splices using Thermofit In-Line Splice Sealing System D-436-52/-53.

2.0 PROCEDURE:

- a) Strip all wires 7.92 (0.312) to 8.74 (0.344).
- b) Attach the single lead to the appropriate size crimp splice using a Raychem AD-1377 Crimp Tool.
- c) Pass the wires to be attached to other barrel through the sealing sleeve from the three-hole insert end.
- d) Insert wires into barrel and crimp. Care must be taken that the wires remain untwisted between the crimp splice and the three wire seal or the sealing sleeve cannot be positioned properly.
- e) Apply heat, using the recommended heat source, first to the three-hole insert and then the other. Heat should be applied until insert melts and flows axially along the wires.

3.0 RECOMMENDED RAYCHEM HEATING TOOLS

Heater	Reflector			
Thermogun #500A Shop Air Heater #CV-4504 Mini-Gun #CV-5300	TG-14 991180 991319			

305			E Connectivity Constitution Drive Park, CA 94025, U		Raychem Products	IN-LINE SPLICE SEALING SYSTEM, 2 OR 3 TO 1 SPLICE: Tin Plated, Color Coded, with Inspection Slots			
UNLESS OTHERWISE SPECIFIED DIMENSIONS ARE IN MILLIMETERS. INCHES DIMENSIONS ARE BETWEEN BRACKETS.					DOCUMENT NO.: D-436-52/-53				
TOLERANCES: 0.00 N/A 0.0 N/A 0 N/A	0.00 N/A 0.0 N/A ROUGHNESS IN		drawing at any time	nnectivity reserves the right to amend this ag at any time. Users should evaluate the lity of the product for their application.		DATE: DOC ISSUE: 2			C ISSUE: 2
DRAWN BY: M. FORONDA		REPL	LACES: DCR		MBER: 0001302	PROD. REV. SEE TABLE	SCALE: None	SIZE:	SHEET: 2 of 2